

LISTA COMPATIBILITÀ WHY LITE

Legenda:  TECNOLOGIA WHY SYNC  AGIRE SULLA RICEVENTE  FUNZIONAMENTO DIRETTO

ACM TX2, TX2 COLOR, TX4 	FAAC XT 433 RC, TE433HG, XT4 433 RCBE 	ROPER NEO 
ADYX TE4433H BLUE, 433-HG BRAVO 	FADINI JUBI-SMALL, JUBI 433, DIVO 71/4 	SABUTOM BROOVER, BROSTAR 
AERF COMPACT, HY-DOM, MERCURI B, MERCURI C, SABUTON, MARS, SATURN, ST3/N, TERRA, TMP-1, TMP-2, UNITECH 	GENIUS BRAVO, ECHO 	SEAV BE HAPPY RS, BE SMART 
ALLMATIC BROWN, BROWN RED, BRO.OVER, PASS, MINIPASS, TECH3, FOR4 	GIBIDI AU1600, AU1600 WOOD, AU1680, AU1680 WOOD, DOMINO, MAKO 	SECULUX NEO 
APRIMATIC TR, TM4, TXM 	JCM NEO, TWIN 	SILVELOX MHz 2007, QUARZ SAW 
AVIDSEN 104251, 104250, 104250 OLD, 104250 RED, 104257, 104350, 654250, TX4 114253 	KBLUE ETH-TEL01 	SIMINOR CVXNL, MITTO 
BENINCA TO. GO. WV, TWV, ROLLKEY, APPLE, LOT WCV, CUPIDO, HAPPY VA, TO.GO. VA 	KEY 900TXB-42R, TXB 44R, SUB 44R 	SIMINOR SIM433 
BENINCA IO 	KING GATES CLIPPER, STYLO 	SOMFY K-EASY, K-EASY NEW, K-EASY OLD, MITTO, KEY GO RTS, TELIS RTS, KEYTIS RTS, KEYTIS RTS NS, ALARMA 
BFT MITTO, MITTO M, MITTO RCB, MITTO A, TRC, GIBLI, MURALE, KLEIO 	KLING KUA, KUA E, KUA S 	STAGNOLI KALLISTO, VENUS AV223 
CASALI GENIUS/CASALI A252RC 	LIFE FIDO 	TAU 250K-SLIMRP, 250K-SLIMR, 250T-4RP 
CLEMSA MUTANCODE, T, T-8, E-CODE N 	MHOUSE TX3, TX4, GTX4 	TOR LIFT TORMIT4 
DASPI ZERO RC 	MOOVO MT4G 	V2 TSC, TXC, TRC, HANDY, PHOENIX, PHOX 433 
DEA SYSTEM PUNTO 278, GOLDR, GENIE R 273, GENIE R-GT2M, MIO TR, GT2M, TRN 	NICE SMILO, FLOR-S, VERY-VR, FLOR-S ERA, INTI, ERGO, PLANO 	VDS ECO-R, TRQ P 
DITEC/ENTREMATI BIXLP, GOL4, BIXLG, ZEN 	NORTON NEO, TXCD 	
DOORHAN TRANSMITTER 4 	NOVOFERM MCHS, MICRO-NOVOTRON 502, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 31, MICRO-NOVOTRON 51, MINI-NOVOTRON 30, MINI-NOVOTRON 50, MNHS, MINI NOVOTRON 522 	
DOORMATIC MILENY, MILENY-EVO 	O&O TX, T.COM R4-2, TWIN, TX (NEO) 	
ECOSTAR RSC, RSE, RSZ 	PRASTEL MTE, MPSTLE, MPSTP2E, TCE, BFOR, TRQ-P, SLIM-E 	
ERREKA IRIS, ROLLER 2, ROLLER 433, SOL433, VEGA 433 	PUJOL Attenzione possibili personalizzazioni non duplicabili TWIN, VARIO, VARIO MARS, VARIO OCEAN, NEO 	
FAAC TML 433SLH, XT 433 SLH, T 433 SLH, XT 433 SLH BLACK 	RIB LITHIO 	

TECNOLOGIA WHY SYNC

In prossimità dell'automazione e prima di aver utilizzato il radiocomando originale, premere e mantenere premuto il tasto del radiocomando WHY LITE fino a quando il led inizierà a lampeggiare. Attendere la fine del lampeggio.

AGIRE IN RICEVENTE

In prossimità dell'automazione e prima di aver utilizzato il radiocomando originale, premere e rilasciare il tasto PRG o PGM presente in ricevente, di seguito premere il tasto del radiocomando WHY LITE.

FUNZIONAMENTO DIRETTO

In prossimità dell'automazione e prima di aver utilizzato il radiocomando originale, premere il tasto del radiocomando WHY LITE 4/5 volte.